



June 12, 2013

Vicsa Safety S.A.
Casa Matriz
Pintor Cicarelli
683-SAN JOAQUÍN SAN
CHILI

Intertek Test Report Number: G100789754CRT-101

Dear Vicsa Staff:

Intertek has completed the evaluation of your Delta Safety Spectacles with Clear Lenses, manufactured by Vicsa Safety S.A. to the Rating of Z87+. The Safety Spectacles were evaluated to the following sections of **American National Standard for Occupational and Educational Personal Eye and Face Protection Devices, ANSI/ISEA Z87.1-2010**: 5.2; 5.2.1(9.6); 5.2.3(9.7); 5.2.4(9.8); 5.2.5; 5.3; 5.4; 6.1.3(9.10); 6.2.2(9.11); 6.2.3(9.12); 6.2.4(9.13). The test samples were received on 6/4/13 in new condition. The evaluations were performed at Intertek in Cortland, NY on 6/7/13 through 6/12/13. The results of these tests are as indicated below.

Sample(s) provided for Evaluation:
21 Pairs of Delta Safety Spectacles with Clear Lenses

<u>Tests Completed:</u>	<u>Test Date(s):</u>	<u>Section</u>	<u>Results</u>
General Requirements (All Protectors)	6/7/13-6/12/13	5.2; 5.2.1; 5.2.3; 5.2.4; 5.2.5; 5.3; 5.4 6.1.3; 6.2.2; 6.2.3;	PASS
Impact Protector Requirements (Z87+)	6/7/13-6/12/13	6.2.4	PASS

NOTE: See Pages 3-7 for the representative data sheets for the product evaluated.

This test report concludes the work for your project outlined under Intertek Quote No: 500396274. If there are any questions regarding this report please contact the undersigned at 607-753-6711.

Tested by:

Erik Sprague
Associate Engineer
Performance Group

Reviewed by:

Brian Bishop
Project Engineer
Performance Group



An independent organization testing for safety, performance, and certification.

This report is for the exclusive use of Intertek's Client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this report. Only the Client is authorized to permit copying or distribution of this report and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. The observations and test results in this report are relevant only to the sample tested. This report by itself does not imply that the material, product, or service is or has ever been under an Intertek certification program.

Intertek, Inc.

3933 US Route 11, Cortland, NY 13045 USA
Telephone: +1 607-753-6711 Fax: +1 607-756-9891 Web: www.intertek.com

INTERTEK TEST DATA SHEETS

Client: Vicsa Safety SA Engineer: Erik Sprague
 Job No.: G100789754 Tested By: Erik Sprague Date: 6/7/2013 – 6/12/2013
 Product: Spectacles Reviewed By: Brian Bishop BB Date: 6/12/2013
 Model No.: Delta Standard: ANSI/ISEA Z87.1-2010
 Description: Safety Spectacles with clear lens
 Sample Control Number: CRT1306040902-001

TRANSCRIBED TEST DATA

Type:	Spectacle: X	Goggle:	Faceshield:	WH Lenses:	FF Respirator:	Removable:
Style:	Plano: X	Rx:	Photochromatic:	Tinted:	Clear: X	Non-Removable: X

Table of Contents:				
Required:	Page(s):	Section:	Test Description:	Pass/Fail:
(X)	1	N/A	Intertek Report No:	N/A
(X)	2	N/A	Table of Contents	N/A
(X)	2	N/A	Equipment List	N/A
(X)	3-7	5.2; 5.2.1; 5.2.3; 5.2.4; 5.2.5; 5.3; 5.4	General Requirements (all protectors)	PASS
(X)	3-7	6.1.3; 6.2.2; 6.2.3; 6.2.4	Impact Protector Requirements (Z87+)	PASS

Equipment List:					
Used:	Equipment:	Manufacturer:	Model No.:	Control No.:	Cal. Due Date:
(X)	Headform	Inspec	EN 168:2001 Medium Head (50 th percentile adult male)	N/A	N/A
(X)	Headform	Inspec	"H" Head	NA	N/A
(X)	6-inch scales	Product Engineering	261-006	R177	4/17/14
(X)	Gram Scale	Denver Instrument	MXX-612	S295	9/26/13
(X)	Calipers	Mitu	0-6"	N460	1/3/14
(X)	Tape Measure	Craftsman	939698	N1049	5/2/13
(X)	Thermocouple / Meter / Rod	Omega	HH21A	T1428	12/21/13
(X)	Balance/Scale	Denver Instrument	DI-4K	S132	12/10/13
(X)	High Mass Impactor (pointed projectile)	Intertek	Z87-2010 High Mass	J143	3/13/14
(X)	Air Cannon	Basic Eng	HVIT	N740	8/3/13
(X)	Ventilation Probe	Intertek	1.5mm x 125mm	J154	8/3/13
(X)	Needle Penetrator	Intertek	Z87-2010 Penetrator	J174	N/A
(X)	Drop Ball	Intertek	Z87-2010 Drop Ball	J147	3/1/14

INTERTEK TEST DATA SHEETS

Client: Vicsa Safety SA Engineer: Erik Sprague
 Job No.: G100789754 Tested By: Erik Sprague Date: 6/7/2013 - 6/12/2013
 Product: Spectacles Reviewed By: Brian Bishop BB Date: 6/12/2013
 Model No.: Delta Standard: ANSI/ISEA Z87.1-2010
 Description: Safety Spectacles with clear lens
 Sample Control Number: CRT1306040902-001

TRANSCRIBED TEST DATA

Type: Spectacle: X	Goggle:	Faceshield:	WH Lenses:	FF Respirator:	Removable:
Style: Plano: X	Rx:	Photochromatic:	Tinted:	Clear: X	Non-Removable: X

Section 5, General Requirements (All Protectors)

Section (Test)	Requirement	Results	Compliance																										
5.2	Physical Requirements: Protectors shall be free from projections, sharp edges or other defects which are likely to cause discomfort or injury during use.	<table border="1"> <tr> <td>Sample #</td> <td align="center">1</td> </tr> <tr> <td align="center" colspan="2">Physical Defects</td> </tr> <tr> <td align="center" colspan="2">NO</td> </tr> </table>	Sample #	1	Physical Defects		NO		PASS																				
Sample #	1																												
Physical Defects																													
NO																													
5.2.1 (9.6)	Drop Ball Impact Resistance: The protector lenses shall not fracture when impacted by a steel ball. A complete device shall fail if any of the following occurs; piece fully detached from inner surface, fracture, penetration of the rear surface, or lens not retained	<table border="1"> <tr> <th align="center" colspan="3">Laboratory Conditions:</th> </tr> <tr> <td>Req'd:</td> <td>Temperature Range 18-28 °C (65-82 °F)</td> <td>Humidity Range 35-65 %</td> </tr> <tr> <td>Actual:</td> <td align="center">69</td> <td align="center">45</td> </tr> </table> <table border="1"> <tr> <th>Sample 9.6:</th> <th>Impact eye Location</th> <th>Fracture, penetration, etc</th> </tr> <tr> <td>(1)</td> <td>Left</td> <td align="center">NO</td> </tr> <tr> <td>(2)</td> <td>Left</td> <td align="center">NO</td> </tr> <tr> <td>(3)</td> <td>Right</td> <td align="center">NO</td> </tr> <tr> <td>(4)</td> <td>Right</td> <td align="center">NO</td> </tr> </table>	Laboratory Conditions:			Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %	Actual:	69	45	Sample 9.6:	Impact eye Location	Fracture, penetration, etc	(1)	Left	NO	(2)	Left	NO	(3)	Right	NO	(4)	Right	NO	PASS		
Laboratory Conditions:																													
Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %																											
Actual:	69	45																											
Sample 9.6:	Impact eye Location	Fracture, penetration, etc																											
(1)	Left	NO																											
(2)	Left	NO																											
(3)	Right	NO																											
(4)	Right	NO																											
5.2.2	Protector Criteria	See section 5.2.1	Info only																										
5.2.3 (9.7)	Ignition: Protectors shall not ignite or continue to glow once the rod is removed. Each externally exposed material (exclusive of textiles or elastic bands) shall be tested.	<table border="1"> <tr> <td>Sample #:</td> <td align="center">5.2.3</td> </tr> </table> <table border="1"> <tr> <th align="center" colspan="3">Laboratory Conditions:</th> </tr> <tr> <td>Req'd:</td> <td>Temperature Range 18-28 °C (65-82 °F)</td> <td>Humidity Range 35-65 %</td> </tr> <tr> <td>Actual:</td> <td align="center">69-71</td> <td align="center">62-64</td> </tr> </table> <table border="1"> <tr> <th>Type</th> <th>Ignition</th> <th>Afterglow</th> </tr> <tr> <td>Lens</td> <td align="center">NO</td> <td align="center">NO</td> </tr> <tr> <td>Frame</td> <td align="center">NO</td> <td align="center">NO</td> </tr> <tr> <td>Foam</td> <td align="center">NO</td> <td align="center">NO</td> </tr> <tr> <td>Rubber</td> <td align="center">NO</td> <td align="center">NO</td> </tr> </table>	Sample #:	5.2.3	Laboratory Conditions:			Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %	Actual:	69-71	62-64	Type	Ignition	Afterglow	Lens	NO	NO	Frame	NO	NO	Foam	NO	NO	Rubber	NO	NO	PASS
Sample #:	5.2.3																												
Laboratory Conditions:																													
Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %																											
Actual:	69-71	62-64																											
Type	Ignition	Afterglow																											
Lens	NO	NO																											
Frame	NO	NO																											
Foam	NO	NO																											
Rubber	NO	NO																											

INTERTEK TEST DATA SHEETS

Client: Vicsa Safety SA Engineer: Erik Sprague
 Job No.: G100789754 Tested By: Erik Sprague Date: 6/7/2013 - 6/12/2013
 Product: Spectacles Reviewed By: Brian Bishop BB Date: 6/12/2013
 Model No.: Delta Standard: ANSI/ISEA Z87.1-2010
 Description: Safety Spectacles with clear lens

Sample Control Number: CRT1306040902-001

TRANSCRIBED TEST DATA

Type: Spectacle: X	Goggle:	Faceshield:	WH Lenses:	FF Respirator:	Removable:
Style: Plano: X	Rx:	Photochromatic:	Tinted:	Clear: X	Non-Removable: X

Section (Test)	Requirement	Results	Compliance																																							
5.2.4 (9.8)	<p>Corrosion Resistance:</p> <p>Metal components used in protectors shall be corrosion resistant to the degree that the function of the protector shall not be impaired by the corrosion. Lenses and electrical components are excluded from these requirements.</p> <table border="1"> <tr> <td>Date/Time:</td> <td>6/11/2013-6/12/2013 @12pm</td> </tr> <tr> <td>6/11/2013</td> <td>Brine solution</td> </tr> <tr> <td>6/11/2013</td> <td>Boil for 15 minutes</td> </tr> <tr> <td>6/11/2013</td> <td>Immerse in room temp solution</td> </tr> <tr> <td>6/11/2013 - 6/12/2013</td> <td>Dry for 24-hours at room temp</td> </tr> <tr> <td>6/12/2013</td> <td>Rinse, air dry, evaluate</td> </tr> </table>	Date/Time:	6/11/2013-6/12/2013 @12pm	6/11/2013	Brine solution	6/11/2013	Boil for 15 minutes	6/11/2013	Immerse in room temp solution	6/11/2013 - 6/12/2013	Dry for 24-hours at room temp	6/12/2013	Rinse, air dry, evaluate	<table border="1"> <tr> <th colspan="3">Laboratory Conditions:</th> </tr> <tr> <td>Req'd:</td> <td>Temperature Range 18-28 °C (65-82 °F)</td> <td>Humidity Range 35-65 %</td> </tr> <tr> <td>Actual:</td> <td>67-71</td> <td>43-47</td> </tr> </table> <table border="1"> <tr> <td>Sample #:</td> <td>2</td> </tr> <tr> <td>Metal Components</td> <td>Function Impaired</td> </tr> <tr> <td>Screw 1</td> <td>NO</td> </tr> <tr> <td>Screw 2</td> <td>NO</td> </tr> </table>	Laboratory Conditions:			Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %	Actual:	67-71	43-47	Sample #:	2	Metal Components	Function Impaired	Screw 1	NO	Screw 2	NO	PASS										
Date/Time:	6/11/2013-6/12/2013 @12pm																																									
6/11/2013	Brine solution																																									
6/11/2013	Boil for 15 minutes																																									
6/11/2013	Immerse in room temp solution																																									
6/11/2013 - 6/12/2013	Dry for 24-hours at room temp																																									
6/12/2013	Rinse, air dry, evaluate																																									
Laboratory Conditions:																																										
Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %																																								
Actual:	67-71	43-47																																								
Sample #:	2																																									
Metal Components	Function Impaired																																									
Screw 1	NO																																									
Screw 2	NO																																									
5.2.5	<p>Minimum Coverage Area:</p> <p>The eyewire and lens shall cover in plain view an area of not less than 40 mm (1.57 in.) in width and 33 mm (1.30 in.) in height (elliptical) in front of each eye, centered on the geometrical center of the lens.</p> <p>Frames designed for small head sizes shall cover in plain view an area of not less than 34 mm (1.34 in.) in width and 28 mm (1.10 in.) in height (elliptical), centered on the geometrical center of the lens.</p> <p>Frames designed for small head sizes shall be tested on the 54 mm (2.13 in.) PD headform and are permitted to have an eye size, including eyewire thickness, as small as 34 x 28 mm (1.34 x 1.10 in.). Frames that are tested using the small headform shall be marked on the frame with the letter "H".</p>	<table border="1"> <tr> <td>Sample #:</td> <td>1</td> </tr> <tr> <td colspan="2">Minimum Coverage</td> </tr> <tr> <td colspan="2">YES</td> </tr> </table>	Sample #:	1	Minimum Coverage		YES		PASS																																	
Sample #:	1																																									
Minimum Coverage																																										
YES																																										
5.3	<p>Minimum Lens Thickness:</p> <p>The minimum lens thickness for specified protector shall be those indicated in Table 3.</p>	<table border="1"> <tr> <td>Sample #:</td> <td>1</td> </tr> <tr> <td>Type: (see table below)</td> <td>2</td> </tr> <tr> <td>Measured Lens Thickness (mm):</td> <td>N/A</td> </tr> </table> <table border="1"> <thead> <tr> <th colspan="3">Table 3 Minimum Lens Thickness</th> </tr> <tr> <th>No.</th> <th>Protector</th> <th>Minimum Thickness</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>Spectacle, Plano</td> <td>≥ 3.0 mm (0.12 in.)</td> </tr> <tr> <td>2</td> <td>Spectacle, Plano, Impact Rated</td> <td>No Minimum Thickness Requirement</td> </tr> <tr> <td>3</td> <td>Spectacle, Prescription</td> <td>≥ 3.0 mm (0.12 in.)</td> </tr> <tr> <td>4</td> <td>Spectacle, Prescription, Impact Rated</td> <td>≥ 2.0 mm (0.08 in.)</td> </tr> <tr> <td>5</td> <td>Goggles</td> <td>≥ 3.0 mm (0.12 in.) Glass ≥ 1.27 mm (0.05 in.), Non-glass</td> </tr> <tr> <td>6</td> <td>Goggles, Impact Rated</td> <td>No Minimum Thickness Requirement</td> </tr> <tr> <td>7</td> <td>Faceshield</td> <td>≥ 1.0 mm (0.04 in.)</td> </tr> <tr> <td>8</td> <td>Faceshield, Impact Rated</td> <td>No Minimum Thickness Requirement</td> </tr> <tr> <td>9</td> <td>Welding Helmets</td> <td>No Minimum Thickness Requirement</td> </tr> </tbody> </table>	Sample #:	1	Type: (see table below)	2	Measured Lens Thickness (mm):	N/A	Table 3 Minimum Lens Thickness			No.	Protector	Minimum Thickness	1	Spectacle, Plano	≥ 3.0 mm (0.12 in.)	2	Spectacle, Plano, Impact Rated	No Minimum Thickness Requirement	3	Spectacle, Prescription	≥ 3.0 mm (0.12 in.)	4	Spectacle, Prescription, Impact Rated	≥ 2.0 mm (0.08 in.)	5	Goggles	≥ 3.0 mm (0.12 in.) Glass ≥ 1.27 mm (0.05 in.), Non-glass	6	Goggles, Impact Rated	No Minimum Thickness Requirement	7	Faceshield	≥ 1.0 mm (0.04 in.)	8	Faceshield, Impact Rated	No Minimum Thickness Requirement	9	Welding Helmets	No Minimum Thickness Requirement	PASS
Sample #:	1																																									
Type: (see table below)	2																																									
Measured Lens Thickness (mm):	N/A																																									
Table 3 Minimum Lens Thickness																																										
No.	Protector	Minimum Thickness																																								
1	Spectacle, Plano	≥ 3.0 mm (0.12 in.)																																								
2	Spectacle, Plano, Impact Rated	No Minimum Thickness Requirement																																								
3	Spectacle, Prescription	≥ 3.0 mm (0.12 in.)																																								
4	Spectacle, Prescription, Impact Rated	≥ 2.0 mm (0.08 in.)																																								
5	Goggles	≥ 3.0 mm (0.12 in.) Glass ≥ 1.27 mm (0.05 in.), Non-glass																																								
6	Goggles, Impact Rated	No Minimum Thickness Requirement																																								
7	Faceshield	≥ 1.0 mm (0.04 in.)																																								
8	Faceshield, Impact Rated	No Minimum Thickness Requirement																																								
9	Welding Helmets	No Minimum Thickness Requirement																																								

INTERTEK TEST DATA SHEETS

Client: Vicsa Safety SA Engineer: Erik Sprague
 Job No.: G100789754 Tested By: Erik Sprague Date: 6/7/2013 - 6/12/2013
 Product: Spectacles Reviewed By: Brian Bishop *bb* Date: 6/12/2013
 Model No.: Delta Standard: ANSI/ISEA Z87.1-2010
 Description: Safety Spectacles with clear lens
 Sample Control Number: CRT1306040902-001 **TRANSCRIBED TEST DATA**

Type:	Spectacle: X	Goggle:	Faceshield:	WH Lenses:	FF Respirator:	Removable:
Style:	Plano: X	Rx:	Photochromatic:	Tinted:	Clear: X	Non-Removable: X

Section (Test)	Requirement	Results	Compliance								
5.4	<p>Marking Requirements:</p> <p>All protectors shall bear the permanent markings in specified locations as shown in Table 4a of the standard. Markings shall follow the sequence shown in Table 4b of the standard. Marking for lens type and use applications shall be required only when claims for protection against the hazard or indicated use are made by the manufacturer.</p> <p>In addition, the components of frames that are intended for prescription protector use shall be marked for size in accordance with the system described in ANSI Z80.5-2004. Fronts shall be marked with the A-dimension (eye size) and DBL.</p>	<table border="1"> <tr> <td>Sample #:</td> <td>1</td> </tr> <tr> <td colspan="2">Markings on Sample</td> </tr> <tr> <td colspan="2">V Z87+U6</td> </tr> <tr> <td>Meets requirements of Table 4a or 4b:</td> <td>YES</td> </tr> </table>	Sample #:	1	Markings on Sample		V Z87+U6		Meets requirements of Table 4a or 4b:	YES	PASS
Sample #:	1										
Markings on Sample											
V Z87+U6											
Meets requirements of Table 4a or 4b:	YES										

Section 6, Impact Protector Requirements (Z87+)

Section (Test)	Requirement	Results	Compliance																
6	Impact Protector Requirements (Z87+)																		
6.1	General																		
6.1.1	<p>Impact Rated Protectors:</p> <p>Shall meet the impact requirements and be marked per Tables 4a and 4b of the standard.</p>	Information only																	
6.1.3 (9.10)	<p>Lateral (side) Coverage:</p> <p>Impact rated protectors shall provide continuous lateral coverage (i.e. no openings greater than 1.5 mm (.06 in.) in diameter) from the edge of the lens to a point not less than 10 mm (0.394 in.) posterior to the corneal plane and not less than 10 mm (0.394 in.) above and not less than 10 mm (0.394 in.) below the horizontal plane centered on the eyes of the headform.</p>	<table border="1"> <tr> <td>Sample #:</td> <td>2</td> </tr> <tr> <td>Location</td> <td>Coverage</td> </tr> <tr> <td>0° Right (random) 10 mm above</td> <td>YES</td> </tr> <tr> <td>90° Right 10mm above</td> <td>YES</td> </tr> <tr> <td>90° Left 10mm above</td> <td>YES</td> </tr> <tr> <td>0° Left (random) 10mm below</td> <td>YES</td> </tr> <tr> <td>90° Right 10mm below</td> <td>YES</td> </tr> <tr> <td>90° Left 10mm below</td> <td>YES</td> </tr> </table>	Sample #:	2	Location	Coverage	0° Right (random) 10 mm above	YES	90° Right 10mm above	YES	90° Left 10mm above	YES	0° Left (random) 10mm below	YES	90° Right 10mm below	YES	90° Left 10mm below	YES	PASS
Sample #:	2																		
Location	Coverage																		
0° Right (random) 10 mm above	YES																		
90° Right 10mm above	YES																		
90° Left 10mm above	YES																		
0° Left (random) 10mm below	YES																		
90° Right 10mm below	YES																		
90° Left 10mm below	YES																		

INTERTEK TEST DATA SHEETS

Client: Vicsa Safety SA Engineer: Erik Sprague
 Job No.: G100789754 Tested By: Erik Sprague Date: 6/7/2013 - 6/12/2013
 Product: Spectacles Reviewed By: Brian Bishop BB Date: 6/12/2013
 Model No.: Delta Standard: ANSI/ISEA Z87.1-2010
 Description: Safety Spectacles with clear lens

Sample Control Number: CRT1306040902-001

TRANSCRIBED TEST DATA

Type: Spectacle: X	Goggle:	Faceshield:	WH Lenses:	FF Respirator:	Removable:
Style: Plano: X	Rx:	Photochromatic:	Tinted:	Clear: X	Non-Removable: X

6.2	Impact Requirements																																						
6.2.2 (9.11)	<p>High Mass Impact:</p> <p>The complete device shall be capable of resisting an impact from a pointed projectile.</p> <p>A complete device shall fail if any of the following occurs; piece fully detached from inner surface, fracture, penetration of the rear surface, lens not retained.</p> <table border="1" style="margin-left: 20px;"> <thead> <tr> <th colspan="3">Impactor- Pointed Projectile</th> </tr> <tr> <th></th> <th>Required</th> <th>Actual</th> </tr> </thead> <tbody> <tr> <td>Weight, (grams)</td> <td>500</td> <td>502</td> </tr> <tr> <td>Drop Height, cm (inch)</td> <td>127 (50")</td> <td>50"</td> </tr> </tbody> </table>	Impactor- Pointed Projectile				Required	Actual	Weight, (grams)	500	502	Drop Height, cm (inch)	127 (50")	50"	<table border="1" style="margin-left: 20px;"> <thead> <tr> <th colspan="3">Laboratory Conditions:</th> </tr> <tr> <td>Req'd:</td> <td>Temperature Range 18-28 °C (65-82 °F)</td> <td>Humidity Range 35-65 %</td> </tr> <tr> <td>Actual:</td> <td>69</td> <td>45</td> </tr> </thead> </table> <table border="1" style="margin-left: 20px;"> <thead> <tr> <th>Sample 9.11:</th> <th>Impact eye Location</th> <th>Fracture, penetration, etc</th> </tr> </thead> <tbody> <tr> <td>(1)</td> <td>Left</td> <td>NO</td> </tr> <tr> <td>(2)</td> <td>Left</td> <td>NO</td> </tr> <tr> <td>(3)</td> <td>Right</td> <td>NO</td> </tr> <tr> <td>(4)</td> <td>Right</td> <td>NO</td> </tr> </tbody> </table>	Laboratory Conditions:			Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %	Actual:	69	45	Sample 9.11:	Impact eye Location	Fracture, penetration, etc	(1)	Left	NO	(2)	Left	NO	(3)	Right	NO	(4)	Right	NO	PASS
Impactor- Pointed Projectile																																							
	Required	Actual																																					
Weight, (grams)	500	502																																					
Drop Height, cm (inch)	127 (50")	50"																																					
Laboratory Conditions:																																							
Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %																																					
Actual:	69	45																																					
Sample 9.11:	Impact eye Location	Fracture, penetration, etc																																					
(1)	Left	NO																																					
(2)	Left	NO																																					
(3)	Right	NO																																					
(4)	Right	NO																																					

6.2.3 (9.12)	<p>High Velocity Impact:</p> <p>The complete device shall be capable of resisting impact from a 6.35 mm (0.25 in) diameter steel ball traveling at the velocity specified in Table 5 (see Appendix A). No contact with the eye of the headform is permitted as a result of the impact.</p> <p>A complete device shall fail if any of the following occurs; piece fully detached from inner surface, fracture, penetration of the rear surface, lens not retained. For the high-velocity test, the unaided eye observes any piece adhering to the contact paste, or observes contact paste on the projectile or complete device.</p> <p>**Complete APPENDIX A prior to testing **</p> <table border="1" style="margin-left: 20px;"> <thead> <tr> <th colspan="3">Steel Ball</th> </tr> <tr> <th></th> <th>Required</th> <th>Actual</th> </tr> </thead> <tbody> <tr> <td>Diameter, mm</td> <td>6.35</td> <td>6.35</td> </tr> <tr> <td>Weight, grams</td> <td>1.06</td> <td>1.05</td> </tr> </tbody> </table> <p align="center">Spectacles: 150 ft/s</p>	Steel Ball				Required	Actual	Diameter, mm	6.35	6.35	Weight, grams	1.06	1.05	<table border="1" style="margin-left: 20px;"> <thead> <tr> <th colspan="3">Laboratory Conditions:</th> </tr> <tr> <td>Req'd:</td> <td>Temperature Range 18-28 °C (65-82 °F)</td> <td>Humidity Range 35-65 %</td> </tr> <tr> <td>Actual:</td> <td>69</td> <td>45</td> </tr> </thead> </table> <p>Sample #: <u>9.12</u></p> <table border="1" style="margin-left: 20px;"> <thead> <tr> <th>#</th> <th>Impact Location</th> <th>Impact Velocity (ft/s)</th> <th>Contact w/ eye</th> </tr> </thead> <tbody> <tr> <td>(1)</td> <td>0° Rt. Eye</td> <td>149.7</td> <td>NO</td> </tr> <tr> <td>(2)</td> <td>30° Rt. Eye</td> <td>149.0</td> <td>NO</td> </tr> <tr> <td>(3)</td> <td>*90° Rt. Eye (above)</td> <td>149.9</td> <td>NO</td> </tr> <tr> <td>(4)</td> <td>0° Lt. Eye</td> <td>149.9</td> <td>NO</td> </tr> <tr> <td>(5)</td> <td>30° Lt. Eye</td> <td>149.3</td> <td>NO</td> </tr> <tr> <td>(6)</td> <td>*90° Lt. Eye (below)</td> <td>149.9</td> <td>NO</td> </tr> </tbody> </table>	Laboratory Conditions:			Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %	Actual:	69	45	#	Impact Location	Impact Velocity (ft/s)	Contact w/ eye	(1)	0° Rt. Eye	149.7	NO	(2)	30° Rt. Eye	149.0	NO	(3)	*90° Rt. Eye (above)	149.9	NO	(4)	0° Lt. Eye	149.9	NO	(5)	30° Lt. Eye	149.3	NO	(6)	*90° Lt. Eye (below)	149.9	NO	PASS
Steel Ball																																																				
	Required	Actual																																																		
Diameter, mm	6.35	6.35																																																		
Weight, grams	1.06	1.05																																																		
Laboratory Conditions:																																																				
Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %																																																		
Actual:	69	45																																																		
#	Impact Location	Impact Velocity (ft/s)	Contact w/ eye																																																	
(1)	0° Rt. Eye	149.7	NO																																																	
(2)	30° Rt. Eye	149.0	NO																																																	
(3)	*90° Rt. Eye (above)	149.9	NO																																																	
(4)	0° Lt. Eye	149.9	NO																																																	
(5)	30° Lt. Eye	149.3	NO																																																	
(6)	*90° Lt. Eye (below)	149.9	NO																																																	

*10 mm above or below the plane of the eyes.

INTERTEK TEST DATA SHEETS

Client: Vicsa Safety SA Engineer: Erik Sprague
 Job No.: G100789754 Tested By: Erik Sprague Date: 6/7/2013 – 6/12/2013
 Product: Spectacles Reviewed By: Brian Bishop BS Date: 6/12/2013
 Model No.: Delta Standard: ANSI/ISEA Z87.1-2010
 Description: Safety Spectacles with clear lens
 Sample Control Number: CRT1306040902-001

TRANSCRIBED TEST DATA

Type:	Spectacle: X	Goggle:	Faceshield:	WH Lenses:	FF Respirator:	Removable:
Style:	Plano: X	Rx:	Photochromatic:	Tinted:	Clear: X	Non-Removable: X

<p>6.2.4 (9.13)</p> <p>Penetration Test (lenses only):</p> <p>Lenses for all complete devises shall be capable of resisting penetration by a weighted needle.</p> <p>A complete device shall fail if any of the following occurs; piece fully detached from inner surface, fracture, penetration of the rear surface, lens not retained.</p>	<p>Needle Penetrator</p> <table border="1"> <thead> <tr> <th></th> <th>Required</th> <th>Actual</th> </tr> </thead> <tbody> <tr> <td>Weight, grams</td> <td>44.2</td> <td>43.95</td> </tr> <tr> <td>Drop Height, cm (inch)</td> <td>127 (50")</td> <td>50"</td> </tr> </tbody> </table>				Required	Actual	Weight, grams	44.2	43.95	Drop Height, cm (inch)	127 (50")	50"	<p>Laboratory Conditions:</p> <table border="1"> <thead> <tr> <th>Req'd:</th> <th>Temperature Range 18-28 °C (65-82 °F)</th> <th>Humidity Range 35-65 %</th> </tr> </thead> <tbody> <tr> <td>Actual:</td> <td>69</td> <td>45</td> </tr> </tbody> </table>			Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %	Actual:	69	45	<p>PASS</p>
		Required	Actual																			
	Weight, grams	44.2	43.95																			
	Drop Height, cm (inch)	127 (50")	50"																			
Req'd:	Temperature Range 18-28 °C (65-82 °F)	Humidity Range 35-65 %																				
Actual:	69	45																				
	<table border="1"> <thead> <tr> <th>Sample 9.13:</th> <th>Impact eye Location</th> <th>Penetration</th> </tr> </thead> <tbody> <tr> <td>(1)</td> <td>Left</td> <td>NO</td> </tr> <tr> <td>(2)</td> <td>Left</td> <td>NO</td> </tr> <tr> <td>(3)</td> <td>Right</td> <td>NO</td> </tr> <tr> <td>(4)</td> <td>Right</td> <td>NO</td> </tr> </tbody> </table>	Sample 9.13:	Impact eye Location	Penetration	(1)	Left	NO	(2)	Left	NO	(3)	Right	NO	(4)	Right	NO						
Sample 9.13:	Impact eye Location	Penetration																				
(1)	Left	NO																				
(2)	Left	NO																				
(3)	Right	NO																				
(4)	Right	NO																				